












# GM-60/72










φ 5 mm  
φ 10mm



30 min







|   | DŁUGOŚĆ | SZEROKOŚĆ | GRUBOŚĆ | ILOŚĆ | KOD | PACZKA |
|---|---------|-----------|---------|-------|-----|--------|
| 1 | 716     | 300       | 18      | 1     |     |        |
| 2 | 716     | 300       | 18      | 1     |     |        |
| 3 | 563     | 299       | 18      | 1     |     |        |
| 4 | 563     | 279       | 18      | 1     |     |        |
| 5 | 563     | 299       | 18      | 1     |     |        |
| 6 | 330     | 596       | 18      | 1     |     |        |
| 7 | 326     | 581       | 3       | 1     |     |        |

