

**12MI100** 

MID FREQUENCY TRANSDUCER MI100 Series

## **KEY FEATURES**

- High power handling: 450 W<sub>AES</sub>
- High sensitivity: 100 dB (1W / 1m)
- Very high efficiency (5,1%)
- Extremely linear frequency response

- Low harmonic distortion
- 3" aluminum voice coil with polymide fiber glass former
- Large magnetic assembly for efficient heat dissipation
- Designed for high quality mid-frequency reproduction





## **TECHNICAL SPECIFICATIONS**

Nominal diameter Rated impedance	300	mm	12 in 8 Ω
Minimum impedance			8 Ω
Power capacity <sup>1</sup>		Z	150 W <sub>AES</sub>
Program power <sup>2</sup>			900 W
Sensitivity	100 dB	1W /	1m @ Z <sub>N</sub>
Frequency range	60 - 4.000 Hz		
Voice coil diameter	76,2	mm	3 in
BI factor			21,6 N/A
Moving mass			0,047 kg
Voice coil length			13,5 mm
Air gap height			10 mm
X <sub>damage</sub> (peak to peak)			24 mm

## **THIELE-SMALL PARAMETERS**<sup>3</sup>

Resonant frequency, f <sub>s</sub>	58 Hz
D.C. Voice coil resistance, R <sub>e</sub>	6,3 Ω
Mechanical Quality Factor, Q <sub>ms</sub>	5,5
Electrical Quality Factor, Q <sub>es</sub>	0,23
Total Quality Factor, Q <sub>ts</sub>	0,22
Equivalent Air Volume to C <sub>ms</sub> , V <sub>as</sub>	64 I
Mechanical Compliance, C <sub>ms</sub>	163 μm / N
Mechanical Resistance, R <sub>ms</sub>	3,3 kg / s
Efficiency, η <sub>0</sub>	5,1 %
Effective Surface Area, S <sub>d</sub>	0,053 m <sup>2</sup>
Maximum Displacement, X <sub>max</sub> <sup>4</sup>	3 mm
Displacement Volume, V <sub>d</sub>	159 cm <sup>3</sup>
Voice Coil Inductance, L <sub>e</sub>	1 mH

Notes:

<sup>1</sup> The power capaticty is determined according to AES2-1984 (r2003) standard.

<sup>2</sup> Program power is defined as power capacity + 3 dB.

<sup>4</sup> The X<sub>max</sub> is calculated as  $(L_{vc} - H_{ag})/2 + (H_{ag}/3,5)$ , where  $L_{vc}$  is the voice coil length and  $H_{ag}$  is the air gap height.

<sup>&</sup>lt;sup>3</sup> T-S parameters are measured after an exercise period using a preconditioning power test. The measurements are carried out with a velocity-current laser transducer and will reflect the long term parameters (once the loudspeaker has been working for a short period of time).





[dB] <u>כ</u> 1 k 10 k [Hz]

Note: Frequency response measured with loudspeaker standing on infinite baffle in anechoic chamber, 1W @ 1m  $\,$ 

MOUNTING INFORMATION				
Overall diameter	312 mm	12,3 in		
Bolt circle diameter	294,5 mm	11,6 in		
Baffle cutout diameter:				
- Front mount	278 mm	10,9 in		
Depth	135 mm	5,4 in		
Net weight	7,2 kg	15,8 lb		
Shipping weight	8 kg	17,6 lb		

MOUNTING INFORMATI

## **DIMENSION DRAWING**



