Anesthesia Machine



Your pneumatic solution for surgeries in **close quarters**

The compact Excel 110 and 210 come standard with O₂ and N₂O, as well as a Hypoxic Guard and a GMS absorber. The Excel 210 also includes medical air.



► A Quick Look

Features

- Accommodates three gases and two vaporizers
- Powerful ventilation and monitoring capabilities for secondary anesthetizing locations.

Options

- 7800 Electronic Ventilator with Tek 5 Vaporizers
- 7000 Ventilator with Tek 4 Vaporizers
- New Sigma Delta Vaporizer



Ohmeda Excel 110/210

Anesthesia Machine

Equipment for the way you operate

Specifications for the Excel 110

Weight (approximate)	270 lbs. (122 kg)
Options	
–Vaporizer	17 lbs. (7.6 kg)
–Absorber	21 lbs. (9.5 kg)
–Ventilator	19 lbs. (8.5 kg)
	_

Dimensions

Height	66" (168 cm)
	from floor to upper most part of top shelf
Depth	30" (76 cm)
·	with casters and brake bar

Vidth	
–Machine only	20" (50.7 cm)
-Machine with monitor pod	27" (68 cm)
-Absorber and Absorber Arm	Add 10" (25.5 cm)

Shelving Systems

			•	-
M	idd	le	Sh	elf

-Maximum Load	24 lbs. (11 kg)
-Usable height	6" (15.2 cm)
–Shelf Size	16.6" x 12.5" (42 cm x 31.7 cm)
	varies slightly with shelf style
Top Shelf	
-Maximum Load	48 lbs. (22 kg)
–Shelf Size	21.5" x 14.2" (54.5 cm x 36 cm)
	varies slightly with shelf style
Table-top	
-Height (above floor)	33.5" (84 cm)
–Size	20" x 11.7" (50.8 cm x 29 cm)
	varies slightly with shelf style

Drawer Cabinet

-Contains two 15.5" x 10.5" x 4" (39.4 cm x 26.7 cm x 10.2 cm)

Absorber Post Mounting Assembly

-Absorber Arm Length	14" (35.5 cm)
	varies slightly with arm style
-	10" to 26" (25.4 cm to 66 cm)
–Horizontal Adj	6.5" to 11" (16.5 cm to 27.9 cm)
Casters	
Diameter	5" (12 7 cm)

front casters have a foot-operated brake-bar lock

Common Gas Outlet

-Equipped with a latching, positive engagement, bayonet type connector. The common gas outlet connector will also accept standard 22 mm OD or 15 mm ID conical friction fit connectors.

Specifications for the Excel 210

	300 lbs. (136 kg)
Options	
	17 lbs. (7.6 kg)
–Absorber	21 lbs. (9.5 kg)
–Ventilator	19 lbs. (8.5 kg)
	_
Dimensions	
Height	66" (168 cm)
from t	floor to upper most part of top shelf
	30" (76 cm)
•	with casters and brake bar
Width	
–Machine only	22" (55.8 cm)
-Machine with monitor nod	29" (73.6 cm)
	Add 10" (25.5 cm)
	1Add 10 (25.5 cm)
Shelving Systems	
Middle Shelf	
	24 lbs (11 kg)
	24 lbs. (11 kg)
	6" (15.2 cm)
-Shelf Size	18.6" x 12.5" (47.2 cm x 31.7 cm)
	varies slightly with shelf style
Top Shelf	
-Maximum Load	48 lbs. (22 kg)
–Shelf Size	23.5" x 14.2" (59.6 cm x 36 cm)
	varies slightly with shelf style
Table-top	<i>z</i> , ,
–Height (above floor)	33.5" (84 cm)
	21.7" x 11.7" (55 cm x 29 cm)

Drawer Cabinet

-Contains two 15.5" x 10.5" x 4" (39.4 cm x 26.7 cm x 10.2 cm) drawers

Absorber Post Mounting Assembly

–Absorber Arm Length	14" (35.5 cm)
	varies slightly with arm style
-Vertical Adj (above floor)	10" to 26" (25.4 cm to 66 cm)
-Horizontal Adj	6.5" to 11" (16.5 cm to 27.9 cm)
Casters	
Casters	

front casters have a foot-operated brake-bar lock

Common Gas Outlet

Diameter ____

-Equipped with a latching, positive engagement, bayonet type connector. The common gas outlet connector will also accept standard 22 mm OD or 15 mm ID conical friction fit connectors.



varies slightly with shelf style

5" (12.7 cm)