



# **MASTER PL-S 4 Pin**

# MASTER PL-S 11W/840/4P 1CT/5X10BOX

MASTER PL-S is an efficient low-wattage compact fluorescent lamp, typically used for decorative and orientation purposes. The original Philips-invented bridge technology guarantees optimum performance in the application, enabling more light and higher efficacy than the bended technology. The 4-pin version is designed for operation on electronic gear and is provided with a plug-in/pull-out lamp base.

#### **Product data**

General Information	
Cap-Base	2G7 [ 2G7]
Life to 50% Failures Preheat (Nom)	13000 h
LSF Preheat 2000 h Rated	99 %
LSF Preheat 4000 h Rated	98 %
LSF Preheat 6000 h Rated	97 %
LSF Preheat 8000 h Rated	92 %
LSF Preheat 16000 h Rated	30 %
Light Technical	
Color Code	840 [ CCT of 4000K]
Luminous Flux (Nom)	900 lm
Luminous Flux (Rated) (Nom)	900 lm
Color Designation	Cool White (CW)
Chromaticity Coordinate X (Nom)	381
Chromaticity Coordinate Y (Nom)	379
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (Rated) (Nom)	82 lm/W
Color Rendering Index (Nom)	82
LLMF 2000 h Rated	95 %
LLMF 4000 h Rated	92 %

LLMF 6000 h Rated	90 %
LLMF 8000 h Rated	88 %
LLMF 12000 h Rated	86 %
Operating and Electrical	
Power (Rated) (Nom)	11.6 W
Lamp Current (Nom)	0.160 A
Temperature	
Design Temperature (Nom)	28 °C
Overfeele and Pleasele a	
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Cap-Base Information	4 Pins
Approval and Application	
Energy Efficiency Label (EEL)	Α
Mercury (Hg) Content (Nom)	1.4 mg

Datasheet, 2017, November 20 data subject to change

# **MASTER PL-S 4 Pin**


Energy Consumption kWh/1000 h	13 kWh
Product Data	
Full product code	871150026122970
Order product name	MASTER PL-S 11W/840/4P 1CT/5X10BOX
EAN/UPC - Product	8711500261229
Order code	927936684011

Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	50
Material Nr. (12NC)	927936684011
Net Weight (Piece)	41.000 g
ILCOS Code	FSD-11/40/1B-E-2G7

## Warnings and Safety

- Lamp light technical and electrical characteristics are influenced by operating conditions, i.e. lamp ambient temperature and operating position as well as applied HF control gear
- Shorter lamp life when often switching and not well pre-heated electrodes
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

#### Dimensional drawing




 Product
 D (max)
 D1 (max)
 A (max)
 B (max)
 C (max)


 MASTER PL-S 11W/840/4P 1CT/
 28 mm
 13 mm
 196 mm
 214 mm
 219.9 mm

 5X10BOX

#### PL-S 11W/840/4P LM

#### Photometric data







Lightcolor /840

Lightcolor /840

# **MASTER PL-S 4 Pin**


## Lifetime





## Life Expectancy 3 h cycle





Lumen Maintenance 3 h + 12 h cycle

