


## Valena Life™ 2 SC/APC fibre optic sockets

Cat. Nos: 7 531 30/7 532 30/7 533 30



### 1. USE

Fibre optic feedthrough sockets are fitted with duplex or double simplex feedthroughs: 2 inputs/2 outputs. They are used for connecting 2 fibres (fitted with their connector). They are supplied with protective caps and fitted with a transparent marker holder.

Number of modules: 2

SC/APC connector

- Singlemode APC


- Insertion loss: 0.2 dB

- Endurance (500 insertions): maximum increase of 0.2 dB

### 2. RANGE

Description	White	Ivory	Aluminium
2 SC/APC FO sockets	7 531 30	7 532 30	7 533 30

### 3. DIMENSIONS (mm)



Cat. Nos.	A	B	C	D
7 531 30 - 7 532 30 - 7 533 30	74.7	74.7	27.25	30.6

### 3. TECHNICAL CHARACTERISTICS

#### ■ 6.1 Mechanical characteristics

Protection against solid bodies and liquids: IP 21

Protection against impacts: IK 04

#### ■ 6.2 Material characteristics

**Casing:** Poly gloss appearance

**Colour:** - White RAL 903

- Ivory RAL 113

- Aluminium

**Material:** - Plate: ABS/PC

- Cover plate: Polycarbonate/ABS

- Zero halogen

- UV resistant

#### ■ 6.4 Climate characteristics

Storage and operating temperature: -5°C to +35°C

### 4. CARE

Clean the surface with a cloth.

Do not use acetone, tar-removing cleaning agents or trichloroethylene.

Resistant to the following products: Hexane (EN 60669-1), methylated spirit, soapy water, diluted ammonia, bleach diluted to 10%, window-cleaning products, pre-impregnated wipes.

**Caution:** Always test before using special cleaning products.