



Simple Lift – Options

Table of contents

250-OPT1

Suction frame rotation lock from 90° to 45°

250-OPT2

Pneumatic suction frame rotation (0 -90°)

250-OPT4

Support feet for IGUs

250-OPT5

Vacuum filter

250-OPT6

Suspension point adjustable pneumatically

250-OPT7

Suspension point adjustment manually

250-OPT10

Ejector modules in each suction cup

250-OPT14

50 mm Offset bars to extend suction cups from suction frame



Lifting your productivity

Simple Lift Option 250-OPT1

Suction frame rotation lock from 90° to 45°

Key features:

- *Compatible with the lifting devices equipped with manual suction frame rotation.*
- *Enables unrestricted manual rotation of the suction frame with lock positions at every 45°, instead of the standard 90° increments.*






Lifting your productivity

Simple Lift Option: 250-OPT2

Pneumatic suction frame rotation (0-90°)

Key features:

- *Pneumatic suction frame rotation from 0 to 90 degrees*
- *Hold-to-run control. Movement occurs only while the button is held down.*
- *The buttons are located on the control panel.*
- *The glass must be gripped at its center to ensure controlled operation of the pneumatic rotation.*






Lifting your productivity

Simple Lift Option: 250-OPT4

Support feet for IGUs

Key features:

- Mechanical support feet for IGUs
- Some of the support feet require tailored suction frame
- Dimensions need to be checked to meet customer's requirements
- Plastic covered support plates
- Manual Adjustments



Lifting your productivity

Simple Lift Option: 250-OPT5

Vacuum filter

Key features:

- *Vacuum filter for separating dust and dirt from the vacuum system.*




Lifting your productivity

Simple Lift Option: 250-OPT6

Suspension point adjustable pneumatically

Key features:

- *Suspension point adjustment for tilting the entire lifting device*
- *Hold-to-run control. Movement occurs only while the button is held down.*
- *The tilt angle of the lifting device differs when unloaded and when under load.*




Lifting your productivity

Simple Lift Option: 250-OPT7

Suspension point adjustment manually

Key features:

- Manual adjustment of the suspension point.
- The adjustment allows the lifting device to be tilted to meet the requirements of the application. The tilt angle of the lifting device differs when unloaded and when under load.
- Designed to be adjusted during the lifting device installation by the mechanics.




Lifting your productivity

Simple Lift Option: 250-OPT10

Ejector modules in each suction cup

Key features:

- *Ejector module in each suction cup allows lifting glass elements of different shapes so that some of the suction cups can be positioned outside the glass element*
- *Each module has vacuum gauge*



Lifting your productivity

Simple Lift Option: 250-OPT14

50 mm Offset bars to extend suction cups from suction frame

Key features:

50 mm Offset bars to extend suction cups from suction frame

