


A combination of multi-function video light bracket manual



Product Features

- Loose adjust the shoulder width of human comfort design.
- Use of environmentally friendly and durable, Ren Xing high degree of engineering ABS plastic manufacturing.
- Multi-purpose, multi-function design.
- Resistance sponge shoulder rest massage pad, to reduce the anti-body weight and body fatigue effects.
- Joints thicken, widen and increase the standard metal screws to prevent the camera and video light damage.

BUY ON
www.cablematic.com

Third· The instructions for use

- ① The spin round screws Songtuo frame shoulder part Comfort adjustable stand, and then fixed tightened.
- ② Department of Insurance strap to prevent the improper use of fall Sizes can be adjusted.
- ③ Open the camera head, align the bottom of the camera, Screw locking hole camera with PTZ received at the screws.
- ④ turn on the video light bracket bar, the video light and Bracket on the slot card lock, free adjustment according to the illumination angle.
- ⑤ The this bracket with tripod support functions, and up and down Angle adjustment activity functions (especially for news in situ interview Shooting, details of the shooting and adjust the self-timer, and other functions).



Unit: (mm)