

AUTOMATIC HAND-DRYER

Information



CABLEmatic



FEATURE

automatic hand-dryer [i.e. air towel] is one of the series in our corporation. It possesses excellent characters, such as large quantity of wind, small noise, high sensitivity and facility, safety, Rapidity for use. It is an advanced and ideal sanitary cleaning apparatus at present time.

It can be extensively use In Hotel, Restaurent, sclen ce-research department, Hospital, public place of enter tainment and sanitary room of every family etc.

When you have washed your hands, put your hands under the wind hole of dryer, which sudenly send out a comfortable warm wind and quickly dry your hands. when put your hands to leave the nole of dryen, it will be automatical tune off. this can prevent crossinfection of diease indeed.

tenitical

Power rating	850W
Temperature of wind	38℃ ± 15℃
Vilocity of wind	8m/sec
Voltage rating	220V ~
Acting aisrance	> 60mm
Delay time	< 5sec
Frequ ency	50Hz
class II appliance	☐
protection water	⚠

MOUNTING METHOD




figure1




figure2

OPERATING METHOD

1. After washing hands, put hands under the wind hold of dryer the warm wind automatically send out.

2. In order to shorten the drying time, before drying can wave the water drip on the hands away, or when on drying rub the hands.



CABLEMATIC

MAINTAIN

1. Dryer must mounted on the steadily unvibrated wall.

2. Don't bump dryer with hard matter and waste it using water.

3. Don't drush the outer covering of dryer with banana oil, alcohol and corrosiveness liquid.

Don't wound or rough the outer covering that be caused by touch it with the sharp or rough matter.

4. If will clean the dirty on the outer covering, supply mains must be turned off, then clean it using towel touch with soap liquid.

5. Unskilled person don't disassemble and repair dryer by himself.

6. On the two end of motor will be added some drip light oil per quarter.