

Goggle Inspection Before and After 40cycles of Autoclave

Autoclave Settings for 1 Cycle: 121°C, 110kPa, 30 minutes

Date Tested: 21 June 2019

Autoclave Cycle	Lens (Visual Inspection)		Frame and Strap (Visual Inspection)		Lens' Anti-Fog property (modified based on GB/T 31726-2015, Thermal Fog test)	
	Photo	Condition	Photo	Condition	Photo	Condition
Before Autoclave		---		---		---
After 10 cycles		No damage / abnormality observed		No damage / abnormality observed		No fogging observed
After 20 cycles		No damage / abnormality observed		No damage / abnormality observed		No fogging observed
After 30 cycles		No damage / abnormality observed		No damage / abnormality observed		No fogging observed
After 40 cycles		No damage / abnormality observed		No damage / abnormality observed		No fogging observed