



ENGLISH

# Product Specification Sheet

**PRODUCT CODE:** PPS215RS

**PRODUCT DESCRIPTION:** Shower Handset Adjustable CHR

**RS CODE:** 7845541

## **1) MATERIAL / APPEARANCE**

*ABS Plastic*

## **2) PRODUCT DIMENSIONS**

*L = 325mm, W = 120mm, H = 85mm & 0.2445 Kg*

## **3) INSTALLATION INSTRUCTIONS AND DETAILS**

### **CAUTION**

*Always check the water temperature before using. The recommended domestic hot water supply temperature should not exceed 65°C.*

*The British Burns Association recommends 37°C to 37.5°C as a comfortable bathing temperature for children. In premises covered by the care standards act 2000, the maximum mixed water outlet temperature is 41°C.*

*Check there are no hidden cables or pipes before drilling holes. Use great care when using power tools near water. The use of a residual current device (RCD) is recommended.*

### **HINT**

*When working near a basin, bath or shower, plug or cover the waste outlet to avoid losing small parts. Take care not to drop accessories or tools into the basin, bath or shower.*

*The showerhead faceplate should be regularly cleaned to remove limescale or debris, which may reduce the performance of the shower. Frequency of cleaning will vary according to local water quality.*

*1. To break away scale on a daily basis rub your thumb over the surface of the showerhead or fixed overhead whilst the shower is running.*

*2. If scale deposits are stubborn, soak the showerhead or fixed overhead in limescale remover and rinse thoroughly before use.*

*Note: The star overhead can only be cleaned by soaking the overhead in proprietary limescale remover and rinse thoroughly before use.*

## **4) PACKAGING**

*PP clam and Paper Insert*

## **5) OUTLINE OF PRODUCTION METHOD**

*Primary production method is extrusion*

## **6) APPROVALS**

*WRAS Approved*