



QUALITEK[®] Everkleen 2015 CLEANER

CORPORATE HEADQUARTERS USA: 315 Fairbank St. Addison, IL • 630-628-8083 or 1-800-365-3750 • FAX 630-628-6543

EUROPE UK: Unit 9 Apex Ct. Bassendale Rd. Bromborough, Wirral CH62 3RE • 44 151 334 0798LF • FAX 44 151 346 1408

ASIA-PACIFIC HEADQUARTERS SINGAPORE: 6 Tuas South St. 5 Singapore 637790 • 65 6785 7757 • FAX 65 6795 7767

PHILIPPINES: Phase I Qualitek Ave. Mariveles, Bataan Philippines C-2106 • 6347 935 4119 • FAX 6347 935 5608

CHINA: 3B/F, YiPa Print Bldg. 351 # JiHua Rd., Buji Shenzhen, China 518112 • 86 755 28522814 • FAX 86 755 28522787

This data is based on information that the manufacturer believed to be reliable and offered in good faith. Qualitek International, Inc. makes no warranties expressed or implied as to its accuracy and assumes no responsibilities and liabilities arising out of its use by others as conditions and methods of use of the products is beyond the control of Qualitek International, Inc. The user must determine the suitability of the product before using it on commercial basis. The warranties extend only to the conformity of the product to the physical descriptions. In no event will Qualitek International, Inc. be responsible for special, incidental and consequential damages whether the claim is in contract, negligence or otherwise. Qualitek specifically disclaims any liability for consequential or incidental damages of any kind, including lost profits.

Description

Everkleen 2015 is a buffered biodegradable cleaner formulated to remove flux residues from circuit board assemblies and electronic parts. It is designed to neutralize organic and inorganic acids, making them soluble in water; plus Everkleen 2015 contains a unique anti-foaming agent to reduce foam. Everkleen 2015 will not attack most plastics, anodized surfaces and will not remove ink markings on components.

Main Features

- ☐ Biodegradable Cleaner
- ☐ Effectively reduces foam

Technical Data

	Specification
Color and Appearance	Clear to yellowish Liquid
Specific Gravity	1.002 ± 0.006
pH (5% Solution)	10.0 – 11.0
Biodegradability	No phosphates, chlorides or bromides
Shelf Life	2 years from DOM

Application

Everkleen 2015 may be used in ultrasonic cleaners, in-line cleaning machines, in dishwashers or wash tubs.

AUTOMATIC IN-LINE CLEANING:

Everkleen 2015 is best for automatic in-line cleaning.

DISHWASHER:

Recommended water temperature is 120 – 150 °F (130°F is optional start-up temperature). Run the solution through the entire cycle. Temperature below 120°F result in longer cleaning times and incomplete residue removal.

Process Control

To ensure a consistent cleanliness level, we recommend checking the pH of the solution and maintain a pH of 10 or above. pH can be maintained by adding more Everkleen 2015 to the wash solution. To obtain the highest efficiency, we recommend to clean regularly the scale build up on the nozzles and immersion heaters. We recommend changing the cleaning solution after 8 hours.

Storage & Shelf Life

Everkleen 2015 should be stored in a cool & dry environment. Shelf life is 2 years from the date of manufacture.

Packaging

Everkleen 2015 is available in 1 & 5 Gallon containers and 55 Gallon drums.

Disposal

Everkleen 2015 contains hazardous ingredients therefore it should be disposed of in accordance with state, local & federal authority requirements.

Qualitek® is a trademark of Qualitek International, Inc.