







MADE IN SPAIN Design by PRILUX



Applications		
Offices	Classrooms	Retail
Home	Large surfaces	Hotels
$\mathbb{C}^{\mathbb{V}}$		
Restaurants	Health care	





# **Specifications (Series luminaires)**

4	Voltage (V)	220-240V	
Hz	Frecuency (Hz)	50-60Hz	
	Current (A)	390mA	
φ	Power factor (Cos fi)	0.93	
	LED number	72	
$\bigcirc$	Dimming	No	

$\longleftrightarrow$	Measures	1.130x80x80mm		
←	Mounting position	Empotrar		
$\varphi_{_{\text{LUM}}}$	Flux (lm)	2.400lm		
	Electrical isolation	CI		
( <sup>270</sup>	Lifetime	L70>50.000h		


	IP Tightness index	IP20
$\odot$	Body color	9006
14	Diffuser Material	PC-O
)	Body	AL

Κ	Colour temperature	4.000K
Ŕ	CRI Colour rendering index	>80

Prilux guarantees a ± 10% tolerance in lig	ht flux measurements.
--	-----------------------

 $\stackrel{ }{\longleftrightarrow}$ 

# Dimensions



eferences							
	W <sub>LED</sub>	W	Г Ц	$\varphi_{_{\text{LED}}}$	Φ <sub>LUM</sub>	К	$\longleftrightarrow$
490498	30W	32W	390mA	3.945lm	2.400lm	4.000K	1.130x80x80mm







 $\bigotimes$ 

2...

#### Photometry



#### **On request**



Available RAL colors (Consult)

# Lynx Led Empotrar



S

 $(\mathbf{j})$ 

# Solutions



# description

Regulation for the contribution of natural light to comply with the requirements of the CTE. Independent control of two lines of dimmable DALI luminaires with sensor to install in a luminaire or surface box. Preconfigured for easy operation.



# description

Ø

Ø

The WAS INDOOR solution is specifically aimed atincreasing the well-being of users in places suchas hospitals, nursing homes, wellness centres, classrooms and offices. The circadian lighting is applied in workplaces to improve visual conditions, comfort and the workers' performance, resulting in a higher productivity and a better development of the company.



# description

Casambi version of our fixtures that enables through any Bluetooth® terminal via free APP that offers the control of flow regulation, color,scene configuration, behavior linked to schedules. Multiple accessories can be configured to work onthe same network to unify the control of one ormore spaces, being able to create groups, scenes and dynamic sequences to measure. The Bluetooth® device is valid for any DALI luminaire.

#### Info

For more information on the different solutions compatible with this luminaire, consult the following BIDI codes or on the web www.prilux.es







j

### Info

You need DALI drive