



 Spe	cifications (Series lumin	aires)			=
4	Voltage (V)	220-240V	${\longleftrightarrow}$	Measures	1.154x80x80mm
Hz	Frecuency (Hz)	50-60Hz	←	Mounting position	Empotrar
	Current (A)	max.390mA			,
φ	Power factor (Cos fi)	Hasta 0,93	ф	Flux (lm)	2.286lm
-	LED number	72/90			,
\bigcirc	Dimming	No		Electrical isolation	CI
00	IP Tightness index	IP20		Lifetime	L70>50.000h
\otimes	Body color	9006			,
1/1	Diffuser Material	AL-SP	_		
[j	Body	AL	_		
		'	_		
K	Colour temperature	4.000K/4.000K	_		
Ø	CRI Colour rendering index	>80	_		

Prilux guarantees a ± 10% tolerance in light flux measurements.


Dimensions \$\int \text{Dimensions}\$



References							
	W _{LED}	W		ф	Ф	K	< ↓→
490399	30W	32W	390mA	3.945lm	2.286lm	4.000K	1.154x80x80mm
490405	30W	32W	390mA	3.945lm	2.400lm	4.000K	1.154x80x80mm
490412	37W	40W	390mA	4.930lm	2.857lm	4.000K	1.432x80x80mm
490429	37W	40W	390mA	4.930lm	3.000lm	4.000K	1.432x80x80mm

Photometry







On request






Presence and brightness sensor (mod. 1x/2x 1.200mm/1.500mm)



Dali

Bluetooth



>80 4.000K



Available RAL colors (Consult)



Solutions S



CTE Pack



description



Regulation for the contribution of natural light to comply with the requirements of the CTE. Independent control of two lines of dimmable DALI luminaires with sensor to install in a luminaire or surface box. Preconfigured for easy operation.

description



The WAS INDOOR solution is specifically aimed atincreasing the well-being of users in places suchas hospitals, nursing homes, wellness centres, classrooms and offices. The circadian lighting is applied in workplaces to improve visual conditions, comfort and the workers' performance, resulting in a higher productivity and a better development of the company.

Bluetooth package

description



Casambi version of our fixtures that enables through any Bluetooth® terminal via free APP that offers the control of flow regulation, color,scene configuration, behavior linked to schedules. Multiple accessories can be configured to work onthe same network to unify the control of one ormore spaces, being able to create groups, scenes and dynamic sequences to measure. The Bluetooth® device is valid for any DALI luminaire.

Info



For more information on the different solutions compatible with this luminaire, consult the following BIDI codes or on the web www.prilux.es



Info	j
You need DALI drive	