

Specifications (Series luminaires)

	Electrical isolation	CII
	Voltage (V)	V
Hz	Frecuency (Hz)	50/60Hz
	Power factor (Cos fi)	Hasta >0,9
	Dimming	DALI-DT8

	IP Tightness index	IP20
	IP installed Sealing rating	IP40
	Body color	White
	Diffuser Material	PMMA
	Body	AL

K	Colour temperature	2700K-6500K
	CRI Colour rendering index	>80
	Opening angle	110°
	UGR	<19

	Measures	595x595x9mm
	Mounting position	Recessed Ceiling
	Cut dimensions	575 x 575

	Operating temperature	-20°C ~ +40°C
---	------------------------------	---------------

	Flux (lm)	max. 4000lm
---	------------------	-------------


	Guarantee	3garantia
---	------------------	-----------

	Lifetime	(L70B50>)50.000h
---	-----------------	------------------


References

	W_{LED}	W	ϕ	ϕ_{LED}	ϕ_{LUM}	K		
708029	36W	40W	>0,9	4953lm	4000lm	2700K-6500K	575 x 575	Yes

Dimensions



Photometry



On request



Emergency kit 3h (mod. 1x/2x
1.200mm/1.500mm)



Bluetooth

Accessories



964562

FRAME WH
RECESSED PLASTER
SILENT LED 60X60CM



164092

WH SURFACE
DRAWER SILENT
LED 60X60CM



207621

STEEL CABLE
SUSPENSION 1M
HF11ED6EXP 1UN



472500

SUSPENSION KIT
1.5M SILENT LED (4
UNITS)



397391

RECESSED CEILING
FRAME HIDDEN
PROFILE SILENT I



483995

MARCO BL
EMPOTRAR SILENT
LED I 60X60X4,3CM



484022

CAJON BL
SUPERFICIE SILENT
LED I 60X60X4,3CM



537933

CABLE ALIM
REGULABLE TRANS
5X0,75 1M 1PC



Solutions

S



BLUETOOTH
Pack

description

Device that enables DALI luminaire control through any Bluetooth® terminal via free APP that offers us control of flow regulation, color, scene configuration, behavior linked to schedules.



Was
Indoor

description

The WAS INDOOR solution is specifically aimed at increasing the well-being of users in places such as hospitals, nursing homes, wellness centres, classrooms and offices. The circadian lighting is applied in workplaces to improve visual conditions, comfort and the workers' performance, resulting in a higher productivity and a better development of the company.

Info 

For more information on the different solutions compatible with this luminaire, consult the following BIDI codes or on the web www.prilux.es