



Since the wall mountingset has two stages, the distances from the wall are indicated in the table below according to the two stages

Product Name	Tube	Height (mm)	Width (mm)	Pipework Center (mm)	Thickness (mm)	Wall to Back (mm)	Wall to Pipe Center (mm)	Wall to Front (mm)
Hamilton	7	580	404	545	51	25/34	37,5/46,50	75,50/84,50
Hamilton	10	580	581	545	51	25/34	37,5/46,50	75,50/84,50
Hamilton	14	580	817	545	51	25/34	37,5/46,50	75,50/84,50
Hamilton	17	580	994	545	51	25/34	37,5/46,50	75,50/84,50
Hamilton	20	580	1171	545	51	25/34	37,5/46,50	75,50/84,50
Hamilton	24	580	1407	545	51	25/34	37,5/46,50	75,50/84,50
Hamilton	5	1780	286	1745	51	25/34	37,5/46,50	75,50/84,50
Hamilton	6	1780	345	1745	51	25/34	37,5/46,50	75,50/84,50
Hamilton	7	1780	404	1745	51	25/34	37,5/46,50	75,50/84,50
Hamilton	8	1780	463	1745	51	25/34	37,5/46,50	75,50/84,50
Hamilton	9	1780	522	1745	51	25/34	37,5/46,50	75,50/84,50