

New for 2018, 2 pc all acrylic surfaces

List Prices Sept 2018
White or Bisque color

Tubs feature built- in overflow chambers , slotted or oval and our special slotted drain.

All plumbing is hidden inside the tub skirt along with water pumps and air blowers for Jetted and Air Jetted tubs. Water suplies for faucets are under the tub skirt. Most Roman Tub Faucets will mount on the tubs. Optional wall or floor mounted faucets.

Two peice all acrylic tubs;	Tub And Drai	Tub And Drain Only NO Faucet!			
Modern Oval end Drain;	Oval end Drain; Soaker Jetted		Air Jetted		
O3660-FSBE	wht, bsq	\$3,000	\$4,500	\$5,000	
O3666-FSBE	wht, bsq	\$3,200	\$4,700	\$5,200	
O3672-FSBE	wht, bsq	\$3,400	\$4,900	\$5,400	
Modern Oval Center side Drain wht, bsq		Soaker		Air Jetted	
O3060-FSBS	wht,bsq	\$2,800	N/A	\$4,800	
O3666-FSBS (68 ")	•	\$3,400	\$4,900	\$5,400	
O3672-FSBS (74 ")	wht,bsq	\$3,600		\$5,600	
Single slipper End Drain		Soaker	Jetted	Air Jetted	
O3060-FSBE (58 ")	wht,bsq	\$2,600	N/A	\$4,600	
Double Slipper arm rest;		Soaker	Jetted	Air Jetted	
306mfscsd	wht,bsq	\$3,600	\$5,100	\$5,600	
Modern Rectangle End Drain;		Soaker	Jetted	Air Jetted	
R3660-FSBE	wht,bsq	\$3,000	\$4,500	\$5,000	
R3666-FSBE	wht,bsq	\$3,200	\$4,700	\$5,200	
R3672-FSBE	wht,bsq	\$3,400	\$4,900	\$5,400	
Modern Rectangle Center Side Drain;		Soaker	Jetted	Air Jetted	
R3660-FSBS	wht, bsq	\$3,000	\$4,500	\$5,000	
R3666-FSBS	wht,bsq	\$3,200	\$5,100	\$5,200	
R3672-FSBS	wht,bsq	\$3,400	\$5,300	\$5,400	
Round Center side Drain		Soaker	Jetted	Air Jetted	
O60-FSNC	wht,bsq	\$3,600	\$5,100	\$5,600	

	Faucet on Tub or Wall; Expression, Edwardian, or Victorian					
Option Details;	Faucet on Floor; Expression modern or Edwardian or Victorian					
	LED Light Flex supplies & shut Offs Foam Insulate tub		\$400	\$400	\$400	
			\$125	\$125	\$125	
			\$200	\$200	\$200	
Add Water Jets	5 to 8 jets depending on model					
		6 V jets	\$350	\$350	\$350	
Add V pad Jets for back Therapy		8 V jets	\$400	\$400	\$400	

\$400

Air jets Number varies with size one jet every 4 " Multiple speeds Auto Purge

LED Light Variable colors, strobe, etc.






Measure height from floor to this point under the bathtub drain hole. This will determine the height from the floor to the top flange of the hub supplied

Cut pipe from floor and connect hub. Required height is from Step 1. Apply some caulk to the top flange of the hub to hold the silicon gasket in place. Lift tub over drain.

www.ICSqualitybaths.com



Seal the top of the drain basket as noted above.
Unscrew pop-up and use a basket wrench to tighten the drain basket into the hub. Allow to dry and then re-attach the pop-up, fill with water and test for leaks



\$400

\$400



Equipment Inside Tubs



